

AC 12P



SIZE :

120x120x25mm (4.72"x4.72"x0.98")

CONSTRUCTION :

- Die-cast aluminum housing
- Glass fiber reinforced plastic:
Impeller are UL 94V-0 rating
- Impedance protected
- Leader wire or Terminal is available

OPERATING TEMPERATURE :

Ball bearing - 30°C to +75°C

Sleeve bearing - 10°C to +70°C

WEIGHT :

330 grams




Specifications

Specifications are subject to change without notice

MODEL NO.	BEARING	RATED VOLTAGE	FREQUENCY	MAX. RATED CURRENT	MAX. INPUT POWER	SPEED R.P.M.	MAX. AIR FLOW		MAX. AIR PRESSURE		NOISE dB-A
		VAC	Hz	mA	W		m³/min	CFM	mmH₂O	IN H₂O	
12P-115LB	Ball	115	50/60	150/130	14/13	1600/2000	1.22/1.53	43.40/53.30	2.10/2.60	0.08/0.10	30/35
12P-115LS	Sleeve										
12P-230LB	Ball	230	50/60	90/80	18/16	1600/2000	1.22/1.53	43.40/53.30	2.10/2.60	0.08/0.10	30/35
12P-230LS	Sleeve										
12P-115HB	Ball	115	50/60	170/150	16/14	2000/2400	1.61/1.86	56.72/65.57	2.64/2.43	0.10/0.09	39/42
12P-115HS	Sleeve										
12P-230HB	Ball	230	50/60	95/85	18/16	2000/2400	1.61/1.86	56.72/65.57	2.64/2.43	0.10/0.09	39/42
12P-230HS	Sleeve										

Dimensions (mm)



Performance Curve

