




## BU 10

Industrial Connectors:Measuring and Testing Equipment:Sockets:4 mm system

### Product description

|               |                                                                                                |
|---------------|------------------------------------------------------------------------------------------------|
| Description   | Bright metal 4 mm diameter nickel-plated brass socket with solder connection.<br>Length 22 mm. |
| Type          | BU 10                                                                                          |
| Order No.     | 930 147 - 000                                                                                  |
| System        | 4 mm system                                                                                    |
| Housing Color | red                                                                                            |

### Drawing



### Technical data

|                     |         |
|---------------------|---------|
| Type of contact     | socket  |
| Type of termination | solder  |
| Rated voltage       | DC 60 V |
| Rated current       | 16 A    |
| Contact resistance  | 5 mOhm  |
| Mounting            | screw   |

### Material

|                          |               |
|--------------------------|---------------|
| Contact material         | brass         |
| Contact surface material | nickel-plated |

### Environmental conditions

|                   |                   |
|-------------------|-------------------|
| Temperature range | -25 °C to +100 °C |
|-------------------|-------------------|

### Inflammability class

|         |        |
|---------|--------|
| Housing | 94 V-0 |
|---------|--------|