



PCB LAYOUT - COMPONENT VIEW



MATERIAL:
HOUSING MATERIAL: PBT
FLAMABILITY RATING: UL94-V0
COLOR: RED
CONTACT MATERIAL: PHOSPHOR BRONZE
CONTACT TYPE: STAMPED
CONTACT PLATING: MATT TIN OVER NICKEL
QUALITY CLASS: 25 MATING CYCLES
PITCH: 2.54 MM PER ROW

ENVIRONNEMENTAL:
OPERATING TEMPERATURE: -40°C UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL:
CURRENT RATING: 1.5A PER PIN (PCB PIN)
WORKING VOLTAGE: 100VAC
INSULATION RESISTANCE: >1000MOHM
DIELECTRIC WITHSTANDING VOLT.: 500VAC/MN
CONTACT RESISTANCE: 10mOHM MAX


STANDARD
UL CERTIFIED: E323964 / MOD. NUMBER 69036817xx7x

SOLDERING:
WAVE PROCESS ONLY

DIMENSION:
DIM.A= 1.27 x No. of Spaces
DIM.B= DIM.A + 3.27
DIM.C= DIM.A + 1.80

AVAILABLE
xx : 4 TO 26 CIRCUITS

PACKAGING:
TUBE

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15			
G								
F	17-JUL-13	PACKAGING	QL					
E	21-NOV-11	DIM B	GG					
D	15-APR-10	PINNING	JP					
C	09-MAR-10	STANDARD	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: MM FEMALE ANGLED CONNECTOR WITH POLARIZATION WITHOUT LATCH	SIZE A4	
B	27-NOV-07	MODIFICATIONS	EC		SCALE:			
A	03-NOV-06	PDF	JP		SHEET: 1/1			WERI PART NO: 690 368 17 xx 72
REV	DATE	FILE	BY		DRAW: EAGER			