




| Part No.  | X = Body Length  |
|-----------|------------------|
| PLP2-125  | 0.125 ( 3.2mm )  |
| PLP2-215  | 0.215 ( 5.5mm )  |
| PLP2-250  | 0.250 ( 6.4mm )  |
| PLP2-350  | 0.350 ( 8.9mm )  |
| PLP2-375  | 0.375 ( 9.5mm )  |
| PLP2-500  | 0.500 ( 12.7mm ) |
| PLP2-625  | 0.625 ( 15.9mm ) |
| PLP2-750  | 0.750 ( 19.0mm ) |
| PLP2-1000 | 1.000 ( 25.4mm ) |
| PLP2-1200 | 1.200 ( 30.5mm ) |

| REV. | DESCRIPTION                            | DATE     | APPROVED |
|------|----------------------------------------|----------|----------|
| P    | Updated Material Callout               | 03/14/11 | T. Y.    |
| R    | Updated General Specifications Note 1. | 10/01/12 | T. Y.    |
|      |                                        |          |          |
|      |                                        |          |          |
|      |                                        |          |          |
|      |                                        |          |          |



2. MATERIAL: POLYCARBONATE, 94V-0, CLEAR. BIVAR MATERIAL CODE 47-CR.
1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101 and BSMC-1001.

|                                                      |                 |                                                                                                                                                                                                    |  |                       |
|------------------------------------------------------|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------|
| STANDARD TOLERANCE<br>( UNLESS OTHERWISE SPECIFIED ) |                 | <div></div> <div>4 THOMAS, IRVINE, CA. 92618</div> <div>TEL: (949) 951-8808    FAX: (949) 951-3974</div>      |  |                       |
| <u>DECIMALS</u>                                      | <u>ANGULAR</u>  |                                                                                                                                                                                                    |  |                       |
| .X    ± .1                                           | X°    ± 1°      | <div></div> <div><b>TITLE:</b>    PRESS-FIT, PANEL MOUNT,<br/>                  LIGHT PIPE, FRONT MOUNT</div> |  |                       |
| .XX    ± .01                                         |                 |                                                                                                                                                                                                    |  |                       |
| .XXX    ± .005                                       |                 |                                                                                                                                                                                                    |  |                       |
| DESIGNED:                                            | DATE:           | <b>PART NO:</b>                                                                                                                                                                                    |  | REVISION:             |
| <b>Michael Chen</b>                                  | <b>01/16/02</b> | <b>PLP2-XXX</b>                                                                                                                                                                                    |  | <b>R</b>              |
| CHECKED:                                             | DATE:           | <b>CAGE CODE : 32559</b>                                                                                                                                                                           |  | <b>SHEET # 1 OF 1</b> |
| <b>E. M. Muldoon</b>                                 | <b>04/26/02</b> | CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.                                                                                                                                                    |  |                       |