



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
H	ECN 3339: CN RELEASE	5/19/02	D.CASTRO
J	ECN 3450: DELETED HEX SCREW DIMS.	8/6/08	D.CASTRO
K	ECN 6638: UPDATED FORMAT, PACKAGING, AND LOGOS	1/25/13	D. DESJARDIN



- NOTES:**
1. CABLE SHALL BE TESTED FOR CONTINUITY.
 2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



CABLES ARE SHIPPED WITH THUMBSCREWS INSTALLED AND FOUR HEX SCREW LOCKS FOR OPTIONAL USE. THUMBSCREWS MAY BE REMOVED EASILY AND THE HEX SCREW LOCKS MOUNTED IN THE CAPTIVE NUTS OF THE CONNECTOR.

WIRING MAP

"P1"		"P2"
1	RED-IN	1
6	RED-GND	6
2	GREEN-IN	2
7	GREEN-GND	7
3	BLUE-IN	3
8	BLUE-GND	8
4	BLACK	4
5	BROWN	5
9	RED	9
10	ORANGE	10
11	YELLOW	11
12	GREEN	12
13	BLUE	13
14	PURPLE	14
15	GRAY	15
SHELL		SHELL

PART NUMBER	FEET [METERS]
CTL3VGAMM-5T	5.0 [1.52]
CTL3VGAMM-10T	10.0 [3.05]
CTL3VGAMM-15T	15.0 [4.57]
CTL3VGAMM-25T	25.0 [7.62]
CTL3VGAMM-50T	50.0 [15.24]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	12/6/00		
	CHECKED BY DFP	1/9/01	CATEGORY AUDIO/VIDEO	
	APPROVED BY ZW	2/7/01	PRODUCT DESCRIPTION CA SVGA HD15M/M SUPER THIN	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CTL3VGAMM-T	REV. K
	SCALE: NONE	CAD FILE: CTL3VGAMM-T.SLDDRW	SHEET 1 OF 1	