





1.27 MAX

"A"

2.54


-X-

CONTACT No 1

"C" MAX

5.08 MAX

0 (M) X



45.72	43.18	8	1-281698-8 *
43.18	40.64	17	1-281698-7
38.10	35.56	15	1-281698-5 *
30.48	27.94	12	1-281698-2 *
25.40	22.86	10	1-281698-0 *
20.32	17.78	8	0-281698-8 *
17.78	15.24	7	0-281698-7
15.24	12.70	6	0-281698-6 *
12.70	10.16	5	0-281698-5 *
10.16	7.62	4	0-281698-4 *
7.62	5.08	3	0-281698-3 *
5.08	2.54	2	0-281698-2
C	A	Nb DE POS	PART NUMBER
DIMENSIONS			

X X Y Y D Z
 ANNEE ————— JOUR (1 A 7)
 year ————— day (1 to 7)
 SEMAINE ————— "D" POUR L'EQUIPE JOUR et "N" POUR CELLE DE NUIT
 week ————— 1 letter "D" for day & "N" for night team

DIMENSIONS: mm 		DWN/DESSINE 22NOV2000 C. COMBEDOUZON		 TE Connectivity			
		CHR/VERIFIE 22NOV2000 T. CORRIOLAN					
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES) 0 PLC/DEC: ± 1 PLC/DEC: ±0.3 3 PLC/DEC: ±0.13 4 PLC/DEC: ±0.013 5 PLC/DEC: ±0.0001 ANGLES: ±°		APVD/APPROUVE 22NOV2000 Y. PETRONIN		NAME TITRE HEADERS HE14, SINGLE ROW, RIGHT ANGLE			
		PRODUCT SPEC SPEC. PRODUIT 108-15053					
		APPLICATION SPEC SPEC. APPLICATION -					
MATERIAL/MATIERE SEE NOTE 4		WEIGHT MASSE APPROX. -		SIZE FORMAT A2	CAGE CODE 00779	DRAWING NO No PLAN C-281698	RESTRICTED TO RESERVE A -
		FINISH/FINITION SEE/VOIR NOTE 3 -		CUSTOMER DRAWING /PLAN CLIENT		UNIFORMED POUR REFERENCE	SCALE 1:1