



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model Number: INTERNET350

Internet Office UPS System - All-in-one SOHO Solution

Highlights

- 6 outlets (3 UPS/surge, 3 surge-only)
- Built-in jacks provide complete 1-line phone/DSL surge protection
- Communications port and free software (web download) facilitate unattended shutdown
- Compact cabinet design fits easily on or under any desk
- \$100,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's INTERNET 350 standby UPS system offers complete protection from blackouts, brownouts and transient surges on both AC and dialup modem lines. Provides seamless battery support during brownouts and power failures with enough runtime to save and shutdown connected equipment without data loss. Offers complete power protection in an ultra-compact, flat-pack housing with an appearance closer to a power strip than other bulky UPS designs. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. DB9 serial port with contact closure messaging enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download from www.tripplite.com, includes bundled DB9 cable. Built-in single line RJ11 phone suppression jacks protect modem, fax machine, cordless phone or other peripheral with standard dialup phone connection. Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation. 350VA/180 watt power handling ability supports entry-level PC systems for several minutes during power fail conditions. 2 year warranty. \$100,000 [connected equipment insurance](#) (USA & Canada only).

Applications

- Basic desktop PCs for home/home-office use, basic audio/video and home entertainment components and other sensitive electronic devices.

Package Includes

- INTERNET 350 Standby UPS System
- Telephone cord
- Instruction manual with warranty information

Features

- INTERNET 350 standby UPS offers protection from blackouts, brownouts and surges on both AC and dialup modem lines
- Provides seamless battery support so that connected equipment can be shutdown without data loss
- 3 battery supported outlets protect computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Lightweight, ultra-compact, flat-pack housing offers an appearance closer to a power strip than most traditional bulky UPS designs
- Attractive stealth black UPS color scheme
- DB9 serial port with contact closure messaging enables automatic system shutdown if power fails while the system runs unattended
- PowerAlert software available via free download from www.tripplite.com, cable included
- Built-in single line RJ11 phone suppression jacks protect peripherals with a standard dialup phone connection, phone cable included
- Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation

- 350VA/180 watt power handling ability supports entry-level PC systems for several minutes during power fail conditions
- Includes attached 6 ft. AC power cord, on/off power switch
- Compatible with 120V/60Hz applications in USA, Canada, Mexico and other countries
- 2 year warranty. \$100,000 [connected equipment insurance](#) (USA & Canada only)

Specifications

OUTPUT	
Frequency compatibility	60 Hz
Output VA	350
Output watts	180
Output nominal voltage	120V AC
Output voltage regulation	LINE MODE: Passes sine wave line voltage from 100-141V to connected equipment unchanged BATTERY MODE: PWM sine wave output 120V +/-5%
Output frequency regulation	LINE MODE: Passes line frequency of 60Hz +/-10% BATTERY MODE: Inverter output regulated to 60Hz +/-0.5Hz
Outlet quantity / type	6 NEMA 5-15R output receptacles (3 with UPS and surge suppression / 3 with surge suppression only)
INPUT	
UPS Input cord length (ft.)	6 ft., 16 gauge
Recommended Electrical Service	15A 120V
Maximum Input Amps (A)	12
Maximum Input Watts	1440
Input connection type	NEMA 5-15P
Voltage compatibility (VAC)	120
BATTERY	
DC system voltage (VDC)	12
Battery Access	User replaceable batteries are accessible via user accessible battery door
Full load runtime	4 minutes (350VA)
Half load runtime	12 minutes (175VA)
Typical battery lifespan	3-6 years, depending on usage
Battery charge	2-4 hours to 90%
LEDS ALARMS & SWITCHES	
Alarms	Two program audible alarm beeps at regular intervals to indicate battery backup operation. Continuous alarm tone indicates the UPS is running on battery power and is nearly depleted. Alarm also sounds during self-test operation.
Switches	Power on/off switch
Front panel LEDs	2 LEDs indicate line power, battery power status
SURGE / NOISE SUPPRESSION	

UPS AC suppression joule rating	Conforms to IEEE 587 / ANSI C62.41 specifications
EMI / RFI AC noise suppression	Yes
AC suppression response time	Instantaneous
Dataline suppression	Single line TEL/DSL surge suppression with RJ-style phone connectors (center 2 wires protected, 260V clamping), includes phone cable
PHYSICAL	
Shipping weight (lbs)	11.8
Shipping weight (kg)	5.4
Unit Dimensions (HWD/in)	4.75 x 13.25 x 8.75
Unit Dimensions (HWD/cm)	12.1 x 33.7 x 22.2
Unit weight (lbs)	10.8
Unit weight (kg)	4.9
Cooling method	Convection
Material of construction	Plastic
Form factors supported	Ultra-compact desk/floor mount
ENVIRONMENTAL	
Relative Humidity	0 to 95%, non-condensing
COMMUNICATIONS	
Network monitoring port	Single built-in DB9 serial port supports on battery, low battery and power restored messaging. Interface supports timed inverter shutoff after unattended shutdown. Compatible with Tripp Lite's PowerAlert and Watchdog service software
Software and cabling included	Includes DB9 serial cable, PowerAlert software available via free download
LINE / BATTERY TRANSFER	
Transfer time from line power to battery mode	2-4 milliseconds
Low voltage transfer to battery power	approx. 100V AC
High voltage transfer to battery power	approx. 141V AC
SPECIAL FEATURES	
Appearance	Attractive black ultra-compact housing
Cold Start	Yes, inverter can be "cold started" to enable temporary AC output during a power failure
CERTIFICATIONS	
Certifications	Tested to UL1778 (USA), cUL (Canada), FCC Class B (emissions), NOM (Mexico), FCC Part 68 / Industry Canada (telecommunications)
WARRANTY	

Product Warranty Period (Worldwide)	2-year limited warranty
Optional Coverage	Optional 3 and 5 year on site or factory warranties available for select opportunities, contact Tripp Lite for more information
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at <http://www.tripplite.com/sku/INTERNET350>.

Copyright © 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[INTERNET350](#)