







| REV. | ECN NO. | REVISIONS                                                                     | DRN. | CKD. | APP. | DATE    |
|------|---------|-------------------------------------------------------------------------------|------|------|------|---------|
| A    | —       | NEW RELEASE                                                                   | ADM  | AV   | N.O. | 3-09-01 |
| B    | —       | ADDED: DETAIL A (MOUNTING PIN MODIFICATIONS) AND CRITICAL DIMENSIONS NOTE (*) | ADM  | DC   | N.O. | 8-29-01 |
| C    | —       | CHANGED DIMS: Ø.115 WAS Ø.116, .016 WAS .010, R.003 WAS R.004.                | ADM  |      |      |         |



SOLDER PAD/HOLES LAYOUT  
(SINGLE COLOR SMT LEDS SHOWN)



SOLDER PAD/HOLES LAYOUT  
(BI-COLOR SMT LEDS SHOWN)



- \* DENOTES CRITICAL DIMENSION OR SPECIFICATION
- NOTES:
1. UNLESS OTHERWISE SPECIFIED, ALL SURFACES MUST HAVE FINISH OF SPI A3 TO B1.
  2. UNLESS OTHERWISE SPECIFIED, SINK MARKS & KNOCKOUT MARKS NOT TO EXCEED .005" RECESSED.
  3. FLASH NOT TO EXCEED .005".
  4. NO BUBBLES IN LIGHTPATH GREATER THAN .005".
  5. GATE VESTIGE TO BE FLUSH TO .010" ABOVE SURFACE.
  6. MARKING FOR CAVITY IDENTIFICATION NOT TO EXCEED .003" RAISED, OR NOT TO EXCEED .005" LOWERED.
  7. UNLESS OTHERWISE SPECIFIED, .003" ROUNDS & FILLETS PERMISSIBLE.
  8. UNLESS OTHERWISE SPECIFIED, 2 DEGREE DRAFT PERMISSIBLE.
  9. DIALIGHT P/N 5151113; TELLABS P/N 150321.
  10. DIALIGHT LIGHT SOURCE P/N'S: SINGLE 597-3XXI-5XX; BI-COLOR 597-77XI-5XX.

|                                                                                                                                                                                                                               |                                   |                                              |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----------------------------------------------|
| THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT. |                                   |                                              |
| SCALE 2:1<br>ALL DIM'S IN: INCHES (MM)                                                                                                                                                                                        | DRAWING NUMBER<br>C-16783         | REV<br>C                                     |
| TOLERANCES:<br>UNLESS OTHERWISE SPECIFIED<br>FRACTIONS: ±1/64<br>DECIMALS (.XX): ±.02<br>DECIMALS (.XXX): ±.015<br>DECIMALS (.XXXX): ±.0005<br>ANGLES: ±1°                                                                    | TITLE<br>LIGHTPIPE, THREE ELEMENT |                                              |
| FINISH:                                                                                                                                                                                                                       | MATERIAL                          |                                              |
| FSCM 83330                                                                                                                                                                                                                    | Dialight                          | 1501 ROUTE 34 SOUTH<br>FARMINGDALE, NJ 07727 |
|                                                                                                                                                                                                                               | SHEET OF                          | FAMILY TABLE:                                |