

★★★★★ Five Star 7000 Series Medium Head Cutters

Made in the U.S.A.

Edge hardened to 63/65 Rockwell "C".

Stainless steel leaf springs – fine cutting of small leads and wires.

WIRE CATCH

add suffix **-W**





7240EW shown

7100 Series Medium Head Cutters with Long Foam Cushion Grips

5 3/4" Medium Round Head Cutters



PART #	CUT TYPE	CUTTING CAPACITY
7140E	Semi-flush	.008" - .042"
7141E	Max flush	.005" - .040"
7142E	Opti-flush	.003" - .032"



7200 Series Medium Head Cutters with ESD Safe Molded Grips



5" Medium Round Head Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7240E	Semi-flush	.008" - .042"
7241E	Max flush	.005" - .040"
7242E	Opti-flush	.003" - .032"





5 3/4" Medium Tapered Head Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7143E	Semi-flush	.008" - .036"
7144E	Max flush	.005" - .036"
7145E	Opti-flush	.002" - .028"





5" Medium Tapered Head Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7243E	Semi-flush	.008" - .036"
7244E	Max flush	.005" - .036"
7245E	Opti-flush	.002" - .028"



5 3/4" Medium Tapered/Relieved Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7146E	Semi-flush	.008" - .036"
7147E	Max flush	.005" - .036"
7148E	Opti-flush	.002" - .028"



5" Medium Tapered/Relieved Cutters

PART #	CUT TYPE	CUTTING CAPACITY
7246E	Semi-flush	.008" - .036"
7247E	Max flush	.005" - .036"
7248E	Opti-flush	.002" - .028"

