




LOC		REV		REVISIONS		DATE	APPD
G	14	P	F	ZONE	LTR	DESCRIPTION	
				D		REV, RDRW, & SM PKG PER 0720-0040-93	4-8-93



AMP WIRE RANGE		UL E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
LR7189 Certified		MILITARY P/N AND CLASS	
22-16 AWG	SOLID OR STRANDED	NOT APPLICABLE	



STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928; COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² (509-3,260) CIR MILS SOLID OR STRANDED

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON : 2 PLC DEC ± 3 PLC DEC ± ANGLES ± -		DR 4-8-93 TA BRINKMAN		NAME AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 4-8-93 DA PATTERSON			
		APPD 4-8-93 DE MILLER			
		APPD 4-8-93 JL MECKLEY			
FINISH TIN PLATE 0.00254L.0001001 MIN THK PER MIL-T-10727		APPLICATION SPEC		TERMINAL, FLANGED SPADE, SOLISTRAND™	
WEIGHT -		SIZE C 00779			
SCALE 10:1		DRAWING NO C-323124			
				SHEET 1 OF 1	

QUANTITY	PACKAGE TYPE	PART NO
100	LOOSE PIECE, BOX	8-323124-1
---	LOOSE PIECE	323124