



UNIT: mm




CABLE BLACK PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
E189529 PLAAWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:

- 1.100% short,open,miswire test
- 2.Conduct resistance:2 Ohm(max)
- 3.insulation resistance:5Mohm(min)
- 4.dielectric test:DC 300V



1PCS/PE BAG

⑨	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑧	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PCS"
⑦	TIE	1	WHITE L=100mm
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO:NM-027)
⑤	OUT JACKET	7g	BEIGE (IV-29#) PVC-40P (MOULD NO:NM-83)
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO:NM-40)
③	CABLE	1	BEIGE (IV-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm L=1780±10mm
②	CONN	1	USB2.0 A FEMALE SHELL:NICKEL PIN G/F SHORT TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 A MALE SHELL:NICKEL PIN G/F 3PCS-TYPE INSULATOR COLOR:WHITE
NO.	NAME	Q' TY	SPECIFICATION

CNC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	102-1010-BE-00180
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	☉