

[< Back](#)

 [RSS](#)
 [Print](#)
 [Email](#)

 [Request More Information](#)

 [Distributor Inventory](#)

Delay Line Filter

Part # 856766

Discontinued

Specifications

Technology	SAW
Frequency (MHz)	942.5
Bandwidth (MHz)	35
Insertion Loss (dB)	25.0
I/O Configuration	SE/SE
Package (mm)	7.0 x 5.0
RoHS	Yes 
Lead Free	Yes
Halogen Free	Yes

Additional Information

Status	Discontinued
--------	--------------

Products

[Amplifiers](#)
[Control Products](#)
[Discrete Transistors](#)
[Filters & Duplexers](#)
[Frequency Converters](#)
[Integrated Products](#)
[Optical Components](#)
[Passives](#)
[Standard Products](#)

Applications

[Mobile Devices](#)
[Network Infrastructure](#)
[Defense & Aerospace](#)
[WLAN / Bluetooth](#)
[Base Station](#)
[Cable / FTTH](#)
[Optical](#)
[Point-to-Point Radio](#)
[VSAT](#)
[GaN Products](#)

Foundry

[Welcome to Foundry Services](#)
[Our Processes](#)
[Assembly & Packaging](#)
[GaN Foundry Technology](#)

Resources

[Application Notes](#)
[Brochures](#)
[Corporate](#)
[Supplier Resources](#)
[Technical Papers](#)
[Videos](#)

Brands

[LowDrift™ / NoDrift™](#)
[QUANTUM Tx™](#)
[Spatium™](#)
[TRITIUM™](#)
[TRIUMF™](#)
[TriConnect®](#)
[TriAccess™](#)

Company

[About Us](#)
[Careers](#)
[Newsroom](#)
[Quality](#)
[Contact Us](#)

