






PRODUCT NO.

SEE TABLE



mat'l. code				surface	tolerance	projection	product family
ISO1302				ISO1101	ISO406	mm	MOD JACK
tolerances unless otherwise specified				tolerances unless otherwise specified		mm	6 POS HORIZONTAL
R S00022 BC L 01/26/00				0.X±0.3		mm	P.C.B. MOD JACK ASSY
S N05-0002 YS 01/07/05				0.XX±0.15		mm	
T N06-0130 LONG 5/15/06				0.XXX±0.05		scale 2.0	
U N08-0097 SH MMD 5/10/08				dr	JANET	01/26/00	dwg no
V ELX-N-010699 SH MMD 03/14/12				engr	TONY CHIEN	01/26/00	sheet 1 of 2
				chr	TONY CHIEN	01/26/00	size
				appd	JENN TSAO	01/26/00	A4
sheet index				revision	sheet	1	2
				type Product Customer Drawing			


PRODUCT NO. (NOTE 1)	POSITIONS LOADED	CONTACT PLATING	HOUSING COLOR	EARS	REMARKS
68898-001/-001LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES	-
68898-001R/-001RLF	ALL	5u" Au + high performance lubricant @ TM	RED	YES	-
68898-001G/-001GLF	ALL	5u" Au + high performance lubricant @ TM	GREEN	YES	-
-002/-002LF	2,3,4,5	5u" Au + high performance lubricant @ TM	BLACK	YES	-
-003/-003LF	3,4	5u" Au + high performance lubricant	BLACK	YES	-
-004/-004LF	2,3,4,5	5u" Au + high performance lubricant	BLACK	YES	-
-005/-005LF	ALL	5u" Au + high performance lubricant	BLACK	YES	-
-006/-006LF	3,4	5u" Au + high performance lubricant @ TM	BLACK	YES	-
-007	2,3,4,5	GXT @ TM	GRAY	YES	OBSOLETE
-008/-008LF	ALL	5u" Au + high performance lubricant	BLACK	NO	-
-009/-009LF	2,3,4,5	1,27um /50u" GXT	BLACK	YES	-
-010/-010LF	ALL	1,27um /50u" GXT	BLACK	YES	-
-011/-011LF	2,3,4,5	2u" GXT	BLACK	YES	-
-012/-012LF	2,3,4,5	6u" GXT	BLACK	YES	-
-013/-013LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES	HI TEMP MATERIAL
-014/-014LF	3,4	6u" GXT	BLACK	YES	
-015/-015LF	3,4	5u" Au + high performance lubricant @ TM	BLACK	NO	
-016/-016LF	2,3,4,5	5u" Au + high performance lubricant @ TM	BLACK	NO	
-017LF	ALL	5u" Au + high performance lubricant @ TM	BLACK	YES	-



VIEW A-A

NOTES :

- WHEN PRODUCT CALLS FOR PACKAGING IN TRAY ORDER THE PRODUCT WITH PART NUMBER 68898-XXXT OR -XXXTLF FOR PACKAGING IDENTIFICATION. FOR PRODUCT NUMBER WITHOUT SUFFIX "T" OR "TLF", THE PRODUCT WILL BE PACKED IN TUBE AS PER DUPONT STANDARD PACKAGING.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD.
- FOR 68898-013/013LF THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOMER.



mat'l. code				surface	tolerance	projection	product family
ISO1302				ISO1101	ISO406		MOD JACK
l	tr	ec	n	dr	date	angle	title
R	S00022	BC	L	01/26/00		0.X±0.3	6 POS HORIZONTAL
S	N05-0002	YS	01/07/05			0.XX±0.15	P.C.B. MOD JACK ASSY
T	N06-0130	LONG	5/15/06	0'±2'		0.XXX±0.05	scale 2.0
U	N08-0097	SH	MMQ	5/10/08	dr	JANET	01/26/00
V	ELX-N-010699	SH	MMQ	03/14/12	engr	TONY CHIEN	01/26/00
					chr	TONY CHIEN	01/26/00
					appd	JENN TSAO	01/26/00
sheet	revision						
index	sheet						

