



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ 4 mm safety system ▶ sockets ▶ 4 mm safety system ▶ VON 20

VON 20

datasheet for VON 20
article number: 930046101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 930 046-101
description:	Fully mating connector ,shatter-proof, flexible insulated sleeve. The tapering sleeve end also serves as kinking protection for the lead. Screw connection up to maximum cable cross-section of 1.5 mm². Nickel-plated brass contact material.
typ:	VON 20 rot/red
system:	4mm system
order number:	930 046-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	screw
rated voltage:	30 VAC / 60 VDC
rated current:	16 A
Please consider derating curve!	
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	
	