


FCI

FCI P/N	"L"
(NOTE 1)	
54175-YXXX	XXX


COMPONENTS		
ITEM	QTY	DESCRIPTION
1	2	MTRJ CONNECTOR, MM
2	1	90° MTRJ BOOT, BLACK
3	"L"	CABLE, 650/1.6mm ZIP



SPECIFICATIONS	
INSERTION LOSS	0.5dB MAX
RETURN LOSS	20dB MIN
FIBER PROTRUSION	100nm MAX
APEX OFFSET	N/A
FIBER UNDERCUT	SEE TELECORDIA GR-326

NOTES:

- 1 FCI PART NUMBER CONSISTS OF THE DWG NO, A DASH, AND A SUFFIX YXXX WHERE Y IS THE UNIT OF LENGTH (Y=M IS METERS, Y=F IS FEET) AND WHERE XXX IS THE LENGTH OF "L"
(EX. 54175-M004 IS 4 METERS IN LENGTH)
2. LENGTH IS MEASURED IN A LINEAR STATE FROM CONNECTOR TIP TO CONNECTOR TIP.

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 Electronics FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	NOMINALS ONLY			projection 	title		
A	V12300	JJK	10/01/01		UNLESS NOTED				CA, MJ90-MJ		
B	V12373	JJK	1/3/01	angles					MM-1.6mm ZIP, TYPE NRA		
C	V20480	JRW	4/1/02						product family FIBER OPTICS		
				dr	J. KILE	10/01/01	scale 1:1	A4	size		code
				enrg	S. CLARK	10/01/01			dwg no		
				chr	S. CLARK	10/01/01			54175		sheet
				appd	S. CLARK	10/01/01					1 of 1
sheet index		revision sheet									

ACAD

PDM: Rev:C

STATUS:Released

Printed: Aug 14, 2008