



MLP24



Wirewound, High Current, Molded, MIL-PRF-27

M27/369 Ferrite Core


PART NUMBER	MIL DASH NUMBER	L μ H @ 1 kHz *	DCR OHMS MAX	CURRENT RATING A DC	INC I A DC
M27/369 FERRITE CORE					
MLP24-101L	01	1.0	0.009	6.27	6.4
MLP24-121L	02	1.2	0.010	5.95	5.8
MLP24-151L	03	1.5	0.011	5.67	5.2
MLP24-181L	04	1.8	0.012	5.43	4.8
MLP24-221L	05	2.2	0.013	5.22	4.3
MLP24-271L	06	2.7	0.014	5.03	3.9
MLP24-331L	07	3.3	0.016	4.70	3.5
MLP24-391L	08	3.9	0.017	4.56	3.2
MLP24-471L	09	4.7	0.022	4.01	2.9
MLP24-561L	10	5.6	0.024	3.84	2.7
MLP24-681L	11	6.8	0.026	3.69	2.5
MLP24-821L	12	8.2	0.028	3.55	2.2
MLP24-102L	13	10	0.033	3.27	2.0
MLP24-122L	14	12	0.037	3.09	1.8
MLP24-152L	15	15	0.040	2.97	1.6
MLP24-182L	16	18	0.044	2.84	1.5
MLP24-222L	17	22	0.050	2.66	1.4
MLP24-272L	18	27	0.070	2.25	1.2
MLP24-332L	19	33	0.075	2.17	1.1
MLP24-392L	20	39	0.084	2.05	1.0
MLP24-472L	21	47	0.104	1.84	0.93
MLP24-562L	22	56	0.130	1.65	0.85
MLP24-682L	23	68	0.145	1.56	0.77
MLP24-822L	24	82	0.152	1.53	0.71
MLP24-103L	25	100	0.208	1.30	0.64

All part numbers provide 15% tolerance on inductance

continued next page

* Measured with no dc current at 1 kHz

MARKING: M27/369-XX (MIL DASH NO.)
MLP24-XXXL (GOWANDA DASH NO.)
24226 (GOWANDA CAGE CODE)
YYWWL (DATE CODE & LOT SYMBOL)



NOTES:

- Operating Temperature Range:
-55° to +130°C
- Current Rating is based on a 45°C temperature rise at an ambient temperature of 85°C
- Incremental Current is the approximate value that will cause a 5% maximum decrease in inductance at a zero dc current
- DWV 1000 Vrms @ Sea Level
500 Vrms @ 70,000 Feet
- Grade 5, Encapsulated
- Weight maximum 2.5 grams

TAPE AND REEL SPECS:

Pcs./Reel maximum:	1000
Pitch between parts:	0.4 in.
Inside tape spacing:	2.5 in.
Class:	2

continued from previous page

MLP24

Wirewound, High Current, Molded, MIL-PRF-27


M27/369 Ferrite Core



PART NUMBER	MIL DASH NUMBER	L μ H @ 1 kHz *	DCR OHMS MAX	CURRENT RATING A DC	INC I A DC
M83446/39 FERRITE CORE					
MLP24-123L	26	120	0.283	1.12	0.58
MLP24-153L	27	150	0.330	1.04	0.52
MLP24-183L	28	180	0.362	0.99	0.48
MLP24-223L	29	220	0.505	0.84	0.43
MLP24-273L	30	270	0.557	0.80	0.39
MLP24-333L	31	330	0.650	0.74	0.35
MLP24-393L	32	390	0.770	0.68	0.32
MLP24-473L	33	470	1.03	0.59	0.29
MLP24-563L	34	560	1.14	0.56	0.27
MLP24-683L	35	680	1.50	0.49	0.25
MLP24-823L	36	820	1.98	0.42	0.22
MLP24-104L	37	1000	2.30	0.39	0.20
MLP24-124L	38	1200	2.55	0.37	0.18
MLP24-154L	39	1500	3.00	0.34	0.16
MLP24-184L	40	1800	4.00	0.30	0.15
MLP24-224L	41	2200	4.40	0.28	0.14
MLP24-274L	42	2700	5.80	0.25	0.12
MLP24-334L	43	3300	6.56	0.23	0.11
MLP24-394L	44	3900	8.63	0.20	0.10
MLP24-474L	45	4700	10.1	0.19	0.09
MLP24-564L	46	5600	11.2	0.18	0.09
MLP24-684L	47	6800	15.0	0.15	0.08
MLP24-824L	48	8200	20.8	0.13	0.07
MLP24-105L	49	10000	23.4	0.12	0.06
MLP24-125L	50	12000	26.0	0.12	0.06
MLP24-155L	51	15000	36.0	0.10	0.05
MLP24-185L	52	18000	40.0	0.09	0.05

All part numbers provide 15% tolerance on inductance

* Measured with no dc current at 1 kHz



NOTES:

- Operating Temperature Range: -55° to +130°C
- Current Rating is based on a 45°C temperature rise at an ambient temperature of 85°C
- Incremental Current is the approximate value that will cause a 5% maximum decrease in inductance at a zero dc current
- DWV 1000 Vrms @ Sea Level
500 Vrms @ 70,000 Feet
- Grade 5, Encapsulated
- Weight maximum 2.5 grams

TAPE AND REEL SPECS:

Pcs./Reel maximum:	1000
Pitch between parts:	0.4 in.
Inside tape spacing:	2.5 in.
Class:	2