



φ172mm**San Ace 172****General Specifications**

- Material Frame: Aluminum, Impeller: Plastics (Flammability: UL94V-1)
- Expected Life Refer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire ⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature -30°C to +70°C (Non-condensing)

φ172mm×150mm×51mm [Mass : 760g] **9E type** **Sidecut type****Specifications** The following nos. **have pulse sensors.**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m³/min] [CFM]		Max. Static Pressure [Pa] [inchH ₂ O]		SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
109E5712K501	12	10.2 to 13.8	2.9	34.8	4,100	8.5	300	243.0	0.976	60	−20 to +60	40,000/60°C
109E5712Y501			2.3	27.6	3,800	8	282	210	0.84	60		
109E5712H501			1.2	14.4	3,050	6.4	226	137.2	0.551	52	−20 to +70	
109E5712F501			0.68	8.16	2,500	5.1	180	95	0.38	47		
109E5712M501			0.48	5.76	2,000	4.2	148	67.6	0.271	41		
109E5724C501	24	20.4 to 27.6	2.3	55.2	4,800	9.9	350	308.0	1.237	66	−20 to +70	
109E5724K501			1.3	31.2	4,100	8.5	300	243.0	0.976	60		
109E5724H501			0.58	13.92	3,050	6.4	226	137.2	0.551	52		
109E5724F501			0.35	8.4	2,500	5.1	180	95	0.38	47		
109E5724M501			0.2	4.8	2,000	4.2	148	67.6	0.271	41		
109E5748C501	48	40.8 to 55.2	1.2	57.6	4,800	9.9	350	308.0	1.237	66	−20 to +60	
109E5748K501			0.7	33.6	4,100	8.5	300	243.0	0.976	60		
109E5748H501			0.28	13.44	3,050	6.4	226	137.2	0.551	52	−20 to +70	
109E5748F501			0.19	9.12	2,500	5.1	180	95	0.38	47		
109E5748M501			0.11	5.28	2,000	4.2	148	67.6	0.271	41		

Models without sensors, or with lock sensors, or PWM control function are available as options. Please refer to the index (p. 466).


Dimensions (unit: mm)**Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**

Options (unit: mm)


Finger Guards

Model : 109-319E Surface treatment : Nickel-chrome plating (silver) Color
: 109-319H : Cation electropainting (black)







Inlet side, Outlet side



Outlet side



Airflow - Static Pressure Characteristics

**109E5712K501****109E5724K501****109E5748K501****109E5712Y501****109E5712H501****109E5724H501****109E5748H501****109E5712F501****109E5724F501****109E5748F501****109E5712M501****109E5724M501****109E5748M501****109E5724C501****109E5748C501**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sanyo Denki:](#)

[109E5724H5J01](#)