






(2.54 mm) .100"

OPP-03-01-T-S-E-AD



OPP-10-01-T-S-E-AD



OPP-07-01-T-S-AD

OPP SERIES

ONE-PIECE POWER INTERFACE

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?OPP

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

BeCu

Plating:

Sn over 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +105 °C

Current Rating:

9.6 A per pin

(1 pin powered)

Voltage Rating:

280 VAC

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Alternative alignment pin available
Contact Samtec.

Note: Some sizes, styles and options are non-standard, non-returnable.

