


PANDUCT® Type G — Slotted Wall Wiring Duct



Type G Slotted Wall Wiring Duct


- Made of rigid PVC (See [pg. 34](#) for material specifications)
- Rated for continuous use temperatures up to 50°C (122°F)
- U.L. Flammability Rating: V-0
- Available in a variety of colors as a standard part†
- Provided with standard mounting holes (dimensions see [pg. 29](#))
- Available without mounting holes (See ordering information below)
- Available with adhesive backing* (See [page 22](#) for details)



Type G— Wiring Duct Standard Colors†:

LG	DG	WH
Light Gray	Dark Gray	White
BL	IB	
Black	Intrinsic Blue	

Colors shown are approximate.



Ordering Information:

- Order number of feet required in multiples of 6 ft or Std. Carton quantities.
- To order duct without mounting holes, add NM to Part Number.
- To order with pressure-sensitive adhesive mounting tape applied, add -A to Part Number.
- Part Number shown for Light Gray LG. To order other colors, substitute WH for White, DG for Dark Gray, BL for Black, and IB for Intrinsic Blue

†See [page 36](#) to determine which sizes are available in each color

Duct Part Number	Duct External Dimensions		Cover Part Number	Duct Std. Ctn. Qty.	Cover Std. Ctn. Qty.	Std. Lgth
	WxH IN.	WxH (mm)				
✓ G.5X.5LG6 ✓ G.5X1LG6	0.69 x .56 0.69 x 1.09	(17.5) x (14.2) (17.5) x (27.1)	C.5LG6	120 ft. 120 ft.	120 ft. 120 ft.	6 ft.
✓ G.75X.75LG6 ✓ G.75X1LG6 ✓ G.75X1.5LG6 ✓ G.75X2LG6	0.94 x 0.83 0.94 x 1.09 0.94 x 1.58 0.94 x 2.09	(23.9) x (21.0) (23.9) x (27.1) (23.9) x (40.0) (23.9) x (53.0)	C.75LG6	120 ft. 120 ft. 120 ft. 120 ft.	120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
G1X1LG6 G1X1.5LG6 G1X2LG6 G1X3LG6 G1X4LG6	1.25 x 1.09 1.25 x 1.59 1.25 x 2.09 1.25 x 3.10 1.25 x 4.10	(31.8) x (27.1) (31.8) x (40.3) (31.8) x (53.0) (31.8) x (78.6) (31.8) x (104.0)	C1LG6	120 ft. 120 ft. 120 ft. 120 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
G1.5X1 LG6 G1.5X1.5LG6 G1.5X2LG6 G1.5X3LG6 G1.5X4LG6	1.75 x 1.09 1.75 x 1.59 1.75 x 2.09 1.75 x 3.10 1.75 x 4.10	(44.5) x (27.1) (44.5) x (40.3) (44.5) x (53.0) (44.5) x (78.6) (44.5) x (104.0)	C1.5LG6	120 ft. 120 ft. 120 ft. 120 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
G2X1 LG6 G2X1.5LG6 G2X2LG6 G2X3LG6 G2X4LG6 G2X5LG6	2.25 x 1.09 2.25 x 1.59 2.25 x 2.09 2.25 x 3.10 2.25 x 4.10 2.25 x 5.11	(57.2) x (27.1) (57.2) x (40.3) (57.2) x (53.0) (57.2) x (78.6) (57.2) x (104.0) (57.2) x (129.7)	C2LG6	120 ft. 120 ft. 120 ft. 60 ft. 60 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
✓ G2.5X3LG6	2.75 x 3.12	(69.9) x (79.2)	C2.5LG6	60 ft.	120 ft.	6 ft.
✓ G3X1LG6 ✓ G3X2LG6 ✓ G3X3LG6 ✓ G3X4LG6 ✓ G3X5LG6	3.25 x 1.09 3.25 x 2.09 3.25 x 3.10 3.25 x 4.10 3.25 x 5.11	(82.6) x (27.6) (82.6) x (53.0) (82.6) x (78.6) (82.6) x (104.0) (82.6) x (129.7)	C3LG6	120 ft. 120 ft. 60 ft. 60 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
✓ G4X1.5LG6 ✓ G4X2LG6 ✓ G4X3LG6 ✓ G4X4LG6 ✓ G4X5LG6	4.25 x 1.58 4.25 x 2.09 4.25 x 3.10 4.25 x 4.10 4.25 x 5.11	(108.0) x (40.0) (108.0) x (53.0) (108.0) x (78.6) (108.0) x (104.0) (108.0) x (129.7)	C4LG6	60 ft. 60 ft. 60 ft. 60 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
✓ G6X4LG6	6.25 x 4.11	(158.8) x (104.4)	C6LG6	60 ft.	120 ft.	6 ft.

*Adhesive tape is not CSA Certified. See [page 29](#) for complete listing of dimensions. ✓=New Sizes

Part Number Nomenclature —

G	.5	X	.5	LG	6
↑	↑		↑	↑	↑
type/style	nominal width (in)		nominal height (in)	color	length (ft)