



2314



2314-X-01-XX-00-00-07-0
Swage mount in .076 hole

- X -	Board Thickness	Length V
1	.031	.045
2	.062	.094
3	.094	.125
4	.125	.156


2511




2511-X-01-XX-00-00-07-0
Swage mount in .076 hole

- X -	Board Thickness	Length V
1	.031	.063
2	.062	.094
3	.094	.125
4	.125	.156

2515/2516




2515-X-01-XX-00-00-07-0
Swage mount in .094 hole



2516-X-01-XX-00-00-07-0
Swage mount in .094 hole

- X -	Board Thickness	Length V
1	.031	.075
2	.062	.105
3	.094	.135
4	.125	.147

2502



2502-X-01-XX-00-00-07-0
Swage mount in .094 hole

- X -	Board Thickness	Length V
1	.031	.080
2	.062	.111
3	.094	.143
4	.125	.174

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
Swage pins are annealed

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: 2XXX - X - 01 - XX - 00 - 00 - 07 - 0

BASIC PART #



SPECIFY PIN FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL ◇

44 300μ" SILVER OVER COPPER ◇

50 300μ" ELECTRO-SOLDER
(60/40 SnPb)