

3-polig, IP 66

Schaltschrankeinbau mit Türkupplung




Entriegelungsstück zur Aufhebung der Türverriegelung siehe Seite 38.



Dauerstrom (I_N/I_{th})	Schaltleistung AC-23B (A)	Frontschild	Artikelnummer	ab Lager lieferbar
3-polig	3 x 400 V			
40 A	15 kW	88 x 88	KG41B T203/12 VE	•
63 A	22 kW	88 x 88	KG64B T203/12 VE	•
80 A	30 kW	88 x 88	KG80 T203/12 VE	•
100 A	37 kW	88 x 88	KG100 T203/12 VE	•
125 A	45 kW	88 x 88	KG125 T203/12 VE	•
160 A	55 kW	88 x 88	KG160 T203/12 VE	•
200 A	75 kW	88 x 88	KG210 T203/13 VE	•
250 A	90 kW	88 x 88	KG250 T203/13 VE	•
315 A	110 kW	88 x 88	KG315 T203/13 VE	•
315 A	132 kW	88 x 88	C316 T203/13 VE	•


Dauerstrom (I_N/I_{th})	Schaltleistung AC-23B (A)	Frontschild	Artikelnummer	ab Lager lieferbar
3-polig	3 x 400 V			
40 A	15 kW	88 x 88	KG41B T103/12 VE	•
63 A	22 kW	88 x 88	KG64B T103/12 VE	•
80 A	30 kW	88 x 88	KG80 T103/12 VE	•
100 A	37 kW	88 x 88	KG100 T103/12 VE	•
125 A	45 kW	88 x 88	KG125 T103/12 VE	•
160 A	55 kW	88 x 88	KG160 T103/12 VE	•
200 A	75 kW	88 x 88	KG210 T103/13 VE	•
250 A	90 kW	88 x 88	KG250 T103/13 VE	•
315 A	110 kW	88 x 88	KG315 T103/13 VE	•
315 A	132 kW	88 x 88	C316 T103/13 VE	•

Lochbild Frontschild




Lochbild Boden (Befestigung auf Normschiene bis KG100)


KG41B–KG100




KG125–C316



KG



C316



Frontschild	Bügel-Ø	Anzahl Schlösser
48 x 48	7	3
	5	4
	8	3
64 x 64	5	4
88 x 88	9	4
130 x 130	9	4

	N	P	D3
KG41B, KG64B	25	70	4,1
KG80, KG100	25	90	5,2
KG125, KG160	36	120	6,4
KG210–KG315	44	142	6,4
C316	104	104	7

	G	H	I	L
KG41B	50	64		190
KG64B	50	64		330
KG80	70	80		380
KG100	70	80	26	450
KG125, KG160	112	108	26	450
KG210–KG315	145	126	25	550
C316	128	150	46	550

Informationen zu KG-Schaltern mit Bolzenanschlüssen finden Sie auf Seite 37.



3-polig



Komplett-/Lagergeräte