

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-05-017969	13DEC05	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Ag PLATING
- 4

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 4 GHz

NOMINAL IMPEDANCE:50 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:

CENTRE CONTACT:1.50 mOhm Max

OUTER CONTACT:0.20 mOhm Max

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A
- 5

MECHANICAL CHARATERISTICS


COUPLING RETENTION FORCE:N/A

CABLE RETENETION FORCE:N/A


DURABILITY:500 Cycles Min
- 6

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC



		1	1	BRASS	△	SLEEVE	4
		2	2	PTFE		INSULATION	3
		1	1	BRASS	△	CONTACT	2
		1	1	BRASS	△	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		△	△				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	13DEC05	tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE	
		CHK S.PARLOW	13DEC05		
DIMENSIONS: mm		APVD F.WHEELER-KING	13DEC05	NAME BNC STRAIGHT ADAPTOR J-J 50 OHM	
		PRODUCT SPEC —			
		APPLICATION SPEC —		SIZE A3	
MATERIAL SEE TABLE		WEIGHT —			
		CUSTOMER DRAWING		DRAWING NO C-1337457	
				RESTRICTED TO —	
				</	