

LOC	DIST	REVISIONS				
E	B	P	LTR	DESCRIPTION	DATE	APVD
			C1	REVISED PER ECO-11-005150	21MAR11	RK HMR

NOTES:

1. ELECTRICAL DATA:
- CONTACT RESISTANCE:

INSULATION RESISTANCE:

CURRENT RATING:

BREAKDOWN VOLTAGE:
- 10 mOhm MAX

100 MOhm MIN at 500VDC

5 AMPS


500 VAC MIN PER MINUTE
2. ENVIRONMENTAL:
- OPERATING TEMPERATURE:

SEALING REQUIREMENTS:
- 20°C TO +80°C



IP67
3. PROD SPEC:
- 108-3641
4. PACKAGING:
- 107-3334
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	BLACK	1
3	PIN CONTACT	BRASS	0.15µm GOLD PLATED OVER NICKEL	5
4	5 CORE CABLE (CORES 22AWG TO UL2464)	PVC JACKET UV RESISTANT	BLACK	1

PIN ASSIGNMENTS
FRONT VIEW




5	GREEN
4	BLACK
3	BLUE
2	WHITE
1	BROWN
PIN	WIRE COLOUR



500	40 mm	M12 STRAIGHT MALE CONNECTOR 0.5m CABLE	1-1838240-1
10000	500 mm	M12 STRAIGHT MALE CONNECTOR 10.0m CABLE	1838240-5
7000	350 mm	M12 STRAIGHT MALE CONNECTOR 7.0m CABLE	1838240-4
5000	250 mm	M12 STRAIGHT MALE CONNECTOR 5.0m CABLE	1838240-3
3000	150 mm	M12 STRAIGHT MALE CONNECTOR 3.0m CABLE	1838240-2
2000	100 mm	M12 STRAIGHT MALE CONNECTOR 2.0m CABLE	1838240-1
DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-

FINISH
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

DWN
H M RAGHAVENDRA

CHK
F.WHEELER-KING

APVD
F.WHEELER-KING

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

22AUG05

15DEC05

15DEC05

TE Connectivity

M12 STRAIGHT MALE CONNECTOR
5 POSITION, PVC CABLE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1838240

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
C1