

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

, 19

LOC DIST
G 14

P F

ZONE

LTR

DESCRIPTION

DATE

APPD

G EC 0720-0279-93

6-18-93

56 BB

REVISIONS


AMP
WIRE RANGE

4 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 1.22±0.08[.048±.003]
FOR 9.70[.382] MAX WIRE INS DIA



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C

VOLTAGE RATING:

-

CIRCULAR MIL AREA:

16.8-26.7mm² [33,100-52,600]
STRANDED

-

QTY

LOOSE PC

324114

PACKAGE TYPE

PART NO

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 4 AWG

SIZE

CAGE CODE

DRAWING NO

SCALE

00779

324114

NTS

SHEET

1 OF 1

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

1-800-522-6752

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

AMP 1470-15 REV 3-92

19 AUG 1993

13:50:02

AMP12368

<UJ128A>DEPT1132>U.DWG1132>U.RBY>U.TERMINYL>U.CUST

CUSTOMER DRAWING