






REV.	DATE	ECR NO.	DESCRIPTION
NC	09/09/10	XXXXXX	INITIAL RELEASE



DETAIL B
SCALE 6.000



1. FREQUENCY RANGE: DC 0-3 GHz
2. VSWR(RETURN LOSS): 1.15, MAX.

9	SHELL	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8	GASKET	RUBBER	RED	1		DRAWN	M.ZHANG						09/09/10
7	RETAINER RING	BRASS	NICKEL	1		CHECKED							
6	SPRING	BER. COPPER	NICKEL	1		ISSUED			PART DESCRIPTION				
5	WASHER	BRASS	NICKEL	1		SHEET	1 OF 1		BNC PCB MOUNT RECEPT. PLUG				
4	INSULATOR	PTFE	NATURAL	1		PART NO. 112759-10							
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1									
2	LEG	STAINLESS STEEL	PASSIVATED	1		DWG. NO. 112759-10 .DWG							
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	C:/CONNEX/112759-10 .DWG		REV.	NC	SIZE	A	SCALE	NA	