

Precision Socket Strip 2,54 mm

Series

006

pitch
2,54




mating pin
size
ø 0,40-0,56
□ 0,25x0,45

max.
pincount
064


Rated current	3,0 A
Rated voltage	150 VRMS / Vdc
Withstand voltage	1000 VRMS for one minute
Material contact	Copper alloy
Material clip	BeCu
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-55°C to +125°C
Max. soldering temper.	260°C for 10 seconds

All dimensions in mm.

Variation




1



2

Contact type (for details please see page 22-23)



Clip style:
S = 4 finger clip

Plating:
T = Sn
F = Au
H = Au 0,75 µ

* No. of contacts:
Variation 1 = 001 - 064
Variation 2 = 002 - 064

Variation (1,2)

No. of contacts *
(001,... - 064)

Contact type
(B1,B2,...)

Clip style

Plating contact (T,F)

Plating clip (F,H)



www.mpe-connector.de

Order code:

006-?-?-?-D-?-?-S?-?-XS0

Mating series	034	038	035	037	367
see page	2-4	2-6	2-7	2-8	2-9