

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	BF2	REVISED PER ECO-17-001607	16MAY2017	RK	PO

1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7519.
2. SWITCH SHOWN IN OPEN POSITION.
3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLACK.
4. STAMPING WILL VARY ON 2 & 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.

- 5

.315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300 $\pm$.010 AT MOUNTING SURFACE.
- 6

ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI







FIG 1

7 OBSOLETE	AS SHOWN	6 1.08 10 9-435626-4
		6 .88 8 9-435626-2
7 OBSOLETE		6 .78 7 9-435626-1
		6 .68 6 9-435626-0
		6 .48 4 8-435626-8
OBSOLETE		6 .38 3 8-435626-7
		6 .28 2 8-435626-6
		6 .88 8 5-435626-5
		6 .58 5 5-435626-2
OBSOLETE		6 .48 4 5-435626-1
OBSOLETE		
SURESEDED		
SUPERSEDED BY 2-435668-9		
7 OBSOLETE		
SURESEDED		
7 OBSOLETE		
OBSOLETE		
OBSOLETE		
SUPERSEDED		
SUPERSEDED BY 2-435668-7		
SUPERSEDED BY 435668-5		
435626-3 SHOWN		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TALLEY 1-2-90		 TE Connectivity											
DIMENSIONS: INCHES		CHK R.MILLER 1-3-90													
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD H.LEITER 1-3-90		NAME SWITCH ASSY, DIP, TYPE C, 7000 SERIES, SPST, LOW PROFILE										
			PRODUCT SPEC —												
			APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO				
	MATERIAL HOUSING & ROCKERS: POLYESTER CONTACTS: BERYLLIUM COPPER		FINISH CONTACTS: PLATED .000030 MIN GOLD IN CONTACT AREA OVER .000050 MIN NICKEL		WEIGHT		A2		00779		C=435626		—		
CUSTOMER DRAWING						SCALE		4:1		SHEET		1 of 1		REV BF2	