

4

3

2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	REVISED PER ECO-17-005566	27APR17	B. J	S. Y

D

PROJ NO. 593-312

C

B

A



D

C

B

A


LOW HALOGEN



- NOTES;
- 1 MATERIAL: HOUSING: L.C.P. (HIGH TEMP. THERMOPLASTIC)
UL 94V-0, NATURAL.
CONTACT: BERYLIUM COPPER.
 - 2 FINISH: CONTACT AREA: 0.0002 MIN GOLD ON
0.0013 MIN ALL OVER NICKEL.
SOLDERING AREA: 0.002 MIN MATTE-TIN
 - 3. POSITION SERIES: SEE TABLE. (SHEET 2)
 - 4. CONN STACK HEIGHT COMBINE OF PLUG "Y" H VS REC "X" H.
STACK HEIGHT = Y + X - 5
 - 5 MANUFACTURE PLANT LOCATION MARK. QINGDAO:
 - 6 CONNECTOR WITH BLACK HOUSING AND POLYIMIDE COVER

CONNECTOR ONLY

RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FLORENCE TAN 14SEP04		TE Connectivity						
DIMENSIONS: mm		CHK ERIC TNG								
		APVD SE IFONG		NAME RCEPTACLE ASSEMBLY 9H TYPE FOR FH 0.8mm PITCH B-T-B CONNECTOR -						
		PRODUCT SPEC 108-5390								
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-5254		SIZE A3	CAGE CODE -	DRAWING NO C-5179009	RESTRICTED TO -	
		0 PLC ±- 1 PLC ±0.30 2 PLC ±0.25 3 PLC ±0.20 4 PLC ±- ±3° ANGLES		WEIGHT -						
MATERIAL 		FINISH 		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 3	REV R

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 3			

SCALE	4:1	SHEET	2 OF 3	REV	R
-------	-----	-------	--------	-----	---

APVD

REV	R
-----	---