

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395126202](#)
Status: **Obsolete**
Description: 3.81mm (.150") Pitch Eurostyle™ Horizontal PCB Header, with Reverse Imprinting, Green Housing, 2 Circuits

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	39512
Application	Wire-to-Board
Comments	with Reverse Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block

Physical

Circuits (Loaded)	2
Entry Angle	N/A
Lock to Mating Part	None
Number of Rows	1
Orientation	Horizontal
PC Tail Length	3.50mm (.138")
PCB Thickness - Recommended	2.50mm (.098")
Panel Mount	No
Pitch - Mating Interface	3.81mm (.150")
Pitch - Termination Interface	3.81mm (.150")
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A


Electrical

Current - Maximum per Contact	8A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Product Specification	PS-39500-001
Sales Drawing	SD-39501-002, SD-39512-001



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[39512Series](#)

Mates With

Most 3.81mm (.150") Pitch Industry Standard Plugs, [39513](#) Vertical Plug, [39510](#) Horizontal Plug