




LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
BD	48				H1	ADDED -4 PER NPR 4837	06/14/93	SB
					J	OBSOLETE -3 AND REV PER EC	27 OCT 00	JK
						OU1D-0248-00		



- 1. CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- 2. CONNECTOR COMPLIES WITH AMP SPEC. 108-40,005 WHERE APPLICABLE.
- 3. FLAME RETARDANT 94V-0 RATED GLASS FILLED NYLON, COLOR: SEE TABLE.
- 4. STEEL PER ASTM A109.
- 5. ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE.



OBSOLETE	SMALL PACK	BLACK	205207-4
	STANDARD	BLUE	205207-3
	STANDARD	BLACK	205207-1
	PACKAGING TYPE	INSERTS COLOR	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSION IN INCHES. TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± 2°		DR 7-19-85 5. WELDON CHK 7-19-85 J. GERACE APPD 7-29-85 L. BREKOSKY APPD 7-31-85 V. KUMAR PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME RECEPTACLE CONNECTOR, SIZE 3, 25 POS., AMPLIMITE™ HDP SIZE CAGE CODE DRAWING NO C 00779 C=205207 SCALE NTS SHEET 1 OF 1		
MATERIAL INSERTS: 3 SHELLS: 4 FINISH SHELLS: 5					

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.