






NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
5. CONTACT MATERIAL: COPPER ALLOW W/SILVER PLATING
6. OPERATING FORCE: 425±100 CM/STANDARD
7. OPERATING TEMP: -30° to 85°C
- ▲ 8. CIRCUIT SP: 3 POSITIONS, 30° INDEX.
9. DIELECTRIC STRENGTH: 1000V RMS min.Ⓢ SEA LEVEL
10. ▲ DENOTES CRITICAL PARAMETER
11. HARDWARE SUPPLIED ON SWITCH— SEE BELOW
STOP RING, LOCKWASHER, & HEXNUT



CONTACT CONFIGURATION
Timing: Non-Shorting (BBM)

RECOMMENDED P.C.B. LAYOUT



TITLE			
KC13A38.001NPS			
E-SWITCH®			
A	13282	RELEASED FOR PRODUCTION	7/11/03
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
1.5:1			
DATE			
7/11/03			
DR			
AR			
DWG			
G527531			
REV			
A			