



Dimensions (In.)


Electrical Specifications:

- Input voltage: 300
- Output voltage: 4000
- DCR (N1): 160mΩ max.
- DCR (N2): 115Ω max.
- Wire (N1): polyurethane enameled copper wire; .23 m/m (2UEW) 11 1/2 TS
- Wire (N2): polyurethane enameled copper wire; .06 m/m (USTC) 500TS
- Core: ferrite core GC1 DRWW 3x12
- Insulating tape: polyester film insulating tape no. 500 E74185(S)
- Wax: fully refined paraffin wax 135/140 F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

422-1304