

Fuses

- Replacement fuses for Fluke DMMs are available from your distributor in 440 mA, 500 mA, 630 mA, 1A, 2A, 3A, 11A, and 15A values. To order direct from Fluke call 1-888-99-FLUKE (U.S.) or contact your distributor.

Model	Fuse Requirements
21/23/75/77-II	P/N 871173; 630 mA 250V in series with either 871202; 3A 600V fuse or fusible resistor; R20 - DO NOT SUBSTITUTE FOR R20. P/N 892583; 15A 600V fuse. Also recommended replacement for units with a fused 10A input using a 20A fuse.
21-III/75-III	P/N 871173; 630 mA 250V and P/N 803293 11A 1000V fuse
76/29/79-II 83/85/87 (S/N < 65650001)	P/N 871207; 1A 600V fuse and P/N 892583; 15A 600V fuse
25/27	P/N 871173; 630 mA 250V fuse in series with P/N 871202; 3A 600V fuse. For units with 10A input using a 20A fuse, use P/N 892583; 15A 600V fuse. 27 CAT III S/N > 7247001; P/N 943121 440 mA; 1000V fuse and P/N 803293; 11A 1000V fuse.
45 (S/N < 7211001)	P/N 871181; 550 mA 250V fuse and P/N 892583; 15A 600V fuse
73-II and 73-III	P/N 892583; 15A 600V fuse
863/865/867/867B 83/85/87 (S/N > 65650001)	P/N 943121; 440 mA 1000V fuse and P/N 803293; 11A 1000V fuse
87-IV/89-IV/187/189 83-III/85-III/87-III/87E-III 23-III/77-III/26-III/79-III 175/177/179	
111/112	P/N 803293; 11A 1000V fuse
712/713/714/715/ 716/717/718	P/N 686527; 125 mA 250V fuse