

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300970262](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Dust-Tight Strain Relief Wide Range Grip, 3/4" NPT, Straight Male, Cable Diameter 13.21-18.54mm (.520-.730"), Approximate Break Strength 204.12kg (450 lbs)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159
UL E76954

General

Product Family Cable Grips
Series [130097](#)
Eye Type N/A
Insulated Yes
NEMA Rating Dust Tight
O-Ring N/A
Overview [Strain-Relief Cord Grips](#)
Product Name Dust-Tight
Type Strain Relief Grip
UPC 78678836508
Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

Physical

Approximate Break Strength 204.12kg (450 lbs)
Bale Length N/A
Body Style Straight
Cable Diameter 13.21-18.54mm (.520-.730")
Color - Grommet N/A
Gender Male
Material - Body Zinc Plated Steel
Material - Grip Galvanized Steel
Mesh Length 0.19m (7.50")
Net Weight 44.890/g
Number of Holes N/A
Thread Size 3/4" NPT

Material Info

Engineering Number 36508

Reference - Drawing Numbers

Sales Drawing SD-130097-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Contained Per -
ED/01/2018 (15
January 2018)
2,4-Di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS 50 Image
ELV Not Relevant
RoHS Phthalates Contained: DEHP

Search Parts in this Series

[130097](#) Series