


Eveready 1212

AAA

SUPER HEAVY DUTY



Industry Standard Dimensions



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)
(No Added Mercury or Cadmium)

Designation: ANSI-24D, IEC-R03

Battery Voltage: 1.5 Volts

Operating Temp: -18°C to 55°C (0°F to 130°F)

Average Weight: 9.7 grams (0.31 oz.)

Volume: 4.0 cubic centimeters (0.2 cubic inch)


Average Capacity: 540 mAh to 0.8 volts
(Rated at 25 mA continuous at 21°C)

Cell: One No. 12 (size "AAA")

Jacket: Metal


Industry Standard Test (21°C)

LIGHTING
5.1 ohm LIF




Industry Standard Tests (21°C)


RADIO
75 ohm 4 hrs/day




REMOTE
24 ohm 15 sec/min 8 hrs/day



PHOTOFLASH
3.6 ohm 24 hrs/day



TAPE / ELECTRONIC GAMES
10 ohm 1 hr/day



Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved