



		1					
LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REV PER ECR-10-007996	19APRIL2010	RC	TM



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

1. STAMP 105 AMP 16 - 14* APPROX AS SHOWN
105 INDICATES STUD SIZE
2. RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
3. WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm²
[2,050-5,180 CIRCULAR MIL AREA] STRANDED
4. MATERIAL: COPPER PER ASTM B-152 ANNEALED
5. FINISH: TIN PLATE 0.00254 [.000100] MIN THK
PER ASTM-B545

100	LOOSE PIECE, BOX SPECIAL (NO WINDOW)	8-53125-5
100	LOOSE PIECE, BOX	8-53125-1
5000	ON TAPE	53125-2
1000	LOOSE PIECE	53125-1
QTY	PACKAGING TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 19APR2010	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK T.MICHIELUTI 19APRIL2010				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M.PECHERKE 19APRIL2010	NAME			
	0 PLC ± -	PRODUCT SPEC	TERMINAL, SHORT SPRING SPADE SOLISTRAND			
	1 PLC ± -	—				
	2 PLC ± -	APPLICATION SPEC				
	3 PLC ± -	—				
	4 PLC ± -	—				
MATERIAL	ANGLES ± -	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=53125	RESTRICTED TO —
	FINISH		CUSTOMER DRAWING			
			SCALE 10:1		SHEET 1 of 1	REV D