

NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:

HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER, GOLD PLATED
PER MIL-G-45204 B TYPE 1
0.00001" [0.000254] THK MINIMUM.


SPRING: STAINLESS STEEL TYPE 302.

2. PERFORMANCE

MAXIMUM CURRENT: 1.0 AMPS
MAXIMUM VOLTAGE: 600 W.V.D.C.
MAXIMUM TEMPERATURE: 200°F (93°C)


3. FEATURES:

HOOK FITS COMPONENTS UP TO Ø0.025" [0.64].
PIN PERMITS CONNECTION TO 0.025" [0.64] SQ.
OR Ø0.030" [0.76] SOCKETS.



ACTUAL SIZE

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		DESCRIPTION	
	APPROVALS		DATE	
	DRAWN		6/09	
	APPROVED BY			
MATERIAL SEE NOTE.			PICO HOOK WITH 0.25 [6.35] POST GOLD PLATED	
FINISH SEE NOTE.			SIZE CODE IDENT NO. DRAWING NO.	
			A 08505 P25COLOR	
NEXT ASSY	USED ON		REV.	
APPLICATION	DO NOT SCALE DRAWING		SCALE 2:1 SHEET 1 OF 1	