

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [82-24-8512](#)
Status: **Active**
Description: 2.50mm Pitch Round Conductor Flat Cable - 24 AWG (7 x 32) Stranded, Topcoat, 12 Circuits, Reel 30.48m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR61126
UL E61522

General

Product Family Cable
Series [24492](#)
Crimp Quality Equipment Yes
Geographic Area Asia
Product Name Ribbon
UPC 800754373128

Physical

Cable Length 30.48m
Circuits (Loaded) 12
Insulation PVC
Packaging Type Reel
Pitch - Termination Interface 2.50mm
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 24
Wire/Cable Type (7x32) Stranded, Topcoat

Electrical

Current - Maximum per Contact N/A
Voltage - Maximum 300V

Material Info

Old Part Number 24492-12-100B

Reference - Drawing Numbers

Sales Drawing SD-24492-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[24492Series](#)

Use With
[42219 SPOX™ IDT Receptacle](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

82-24-8512