


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	220	Vac
OPERATING VOLTAGE RANGE	160 ~ 360	Vac
RATED CURRENT (MAX)	40	mA
MINIMUM SPL @ 10 cm.	90	dBA
RESONANT FREQUENCY	60±15	Hz
TONE OR PULSE RATE	CONTINUOUS	0 PULSE PER SECOND
OPERATING TEMPERATURE	-20 ~ +60	°C
STORAGE TEMPERATURE	-30 ~ +70	°C
HOUSING MATERIAL	ABS UL-94-1/16" HB	—
TERMINAL MATERIAL	LEAD WIRE	—
WEIGHT	31.5	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/2/02	
A	REVISED TEMPLATE	5/6/04	R. W.
B	REVISED VOLTAGE UNITS— Vdc TO Vac	8/30/05	B. R.



NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
AI-299.DWG

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN <i>RABL</i>	5/02
APPROVED <i>S.J.</i>	5/02
DO NOT SCALE DRAWING	



projects®
unlimited

Dayton, Ohio

AUDIO INDICATOR
AI-299

SIZE
A

DRAWING NO.
AI-299

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-299](#)