

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

19




(C) COPYRIGHT 19

BY AMP INCORPORATED, ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
CM	52	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REV & REDWN PER EC 0L30-0125-97	6-12-97	TB	RS

- 1

0.00038 MIN SELECTIVE GOLD PLATING ON INSIDE OF RECEPTACLE OVER NICKEL OVER ALL UNDERPLATE.
2. WIRE RANGE: 0.2 - 0.6 MM² (24 - 20 AWG)
3. INSULATION RANGE: 1.14 - 1.78



SECTION A-A



SECTION B-B

MATTE TIN	0.25 BE COPPER	61276-3
PRE-TIN	0.25 PH BRZ	61276-2
1	0.25 BE COPPER	61276-1
FINISH	MATERIAL	PART NUMBER

1.47	.058	2.29	.090	4.11	.162	-	-
1.359	.0535	1.93	.076	2.92	.115	-	-
1.14	.045	1.91	.075	2.79	.110	-	-
0.25	.010	1.78	.070	2.54	.100	-	-
0.13	.005	1.52	.060	2.41	.095	8.38	.330
0.00038	.000015	1.486	.0585	2.31	.091	4.27	.168
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

SEE TABLE

FINISH

SEE TABLE

DWN
T. BECK
6-12-97

CHK
R. SWING
6-12-97

APVD
A. BEDDICK
6-17-97

PRODUCT SPEC
108-1025

APPLICATION SPEC
114-1008

WEIGHT
-

CUSTOMER DRAWING

SCALE
10:1

SHEET
1 OF 1

REV
F

NAME
RECEPTACLE, .058 DIAMETER, 24-20 AWG, .045-.070 INSULATION, RIGHT ANGLE, LOOSE PIECE, P.C. CONTACT

SIZE
A2

CAGE CODE
00779

DRAWING NO
61276

RESTRICTED TO
-

AMP

AMP Incorporated
Harrisburg, PA 17105-3608