


B Type



Materials and Finish

Body: PBT Thermoplastic,
30% glass filled,
UL94V-0 rated,
black color

Contact Material: Phosphor Bronze,
3 to 6 μ Gold Plated

Electrical Specifications

Contact Current Rating:
3 Amp max.

Contact Resistance:
20 milliohms max.

Dielectric Withstanding Voltage:
AC 650 Volts RMS

Insulation Resistance:
1000 Megohms min.

Temperature Rating:
-55°C to +125°C

Tolerances	
X.X ± 0.25	
X.XX ± 0.15	
Unless Stated	
Otherwise	



S 1 1 0 0 - B

Minl Shunt

2.54 mm Pitch



REVISION	DATE	DESCRIPTION	DRAWN BY	CHECKED BY	UNITS
A	5/5/98	New Drawing	C. Lelva		mm
B	5/6/98	Rev. Plating	REVISED BY	APPROVED BY	DATE
B1	11/19/03	Add Tol block	H. MA		5/5/98

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[S1100-B](#)