










REV.	DESCRIPTION	DATE
A	RELEASE	2012/11/7


NUMBER OF POSITIONS	DIMENSION	
	A	B
08	7.62	14.86
10	10.16	17.40
12	12.70	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
22	25.40	32.64
24	27.94	35.18
26	30.48	37.72
28	33.02	40.26
30	35.56	42.80
34	40.64	47.88
36	43.18	50.42
40	48.26	55.50
44	53.34	60.58
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

NOTES:
Insulator Material: PBT, UL 94V-0
Contact Plating:flash gold
Contact Material: Brass

Current Rating : 1A AC,DC
Contact Resistance: 20MΩ Max.
Dielectric Withstanding: AC 500V
Insulator Resistance: 1000MΩ Min.
Operating Temp.: -40°C~+105°C



14P-64P



UNLESS TOLERANCE			DRAW	BY	CnC Tech,LLC Port NO. 3030-XX-0102-00		
GENERAL	ANGLE		DESIGN	BY			
X. ± 0.30	X.° ± 3.0°		CHECK	BY			
.X ± 0.25	.X° ± 2.0°		APPROVE	BY			
.XX ± 0.20	.XX° ± 1.0°				3030-XX-0102-00		
.XXX ± 0.10	.XXX° ± 0.5°						
SCALE			SHEET	UNIT	3030-XX-0102-00		
1:1			1/1	MM			
DRAW NO:			REV: A				