


PLT.6SM
PLT.7M
HEAD VIEW



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT.6SM	.01 (.3)	.6 (15)	.030 (.76)	.070 (1.8)	.124 (3.1)	.095 (2.4)	.125 (3.2)	2.8 (71)	8 (36)	SUB-MINIATURE	CURVED	.02 (9.0)
PLT.7M	.03 (.8)	.68 (17)	.032 (.8)	.090 (2.3)	.148 (3.8)	.115 (2.9)	.180 (4.6)	3.1 (79)	18 (80)	MINIATURE	CURVED	.04 (16)
PLT1M	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	18 (80)	MINIATURE	CURVED	.07 (32)
PLT1.5M	.06 (1.5)	1.25 (32)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	5.6 (142)	18 (80)	MINIATURE	CURVED	.10 (45)
PLT2M	.06 (1.5)	2.00 (51)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	8.0 (203)	18 (80)	MINIATURE	CURVED	.13 (59)
PLT1.5I	.06 (1.5)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	40 (178)	INTERMEDIATE	CURVED	.14 (64)
PLT2I	.06 (1.5)	2.00 (51)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	8.0 (203)	40 (178)	INTERMEDIATE	CURVED	.20 (91)
PLT2.5I	.06 (1.5)	2.50 (64)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	9.7 (246)	40 (178)	INTERMEDIATE	CURVED	.27 (122)

NOTES:

- 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
- *2) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

						TITLE						
						PAN-TY CABLE TIE - PLT SERIES						
						CUSTOMER DRAWING						
						ITEM REVISION NAME						
						W10001CA/33						
						DATASET FILE NAME		MATERIAL: NYLON 6.6				
						W10001CA/33-SS-5540 SH1						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x : - - - .xxx : .020 (.51) .xx : .02 (.5) ANGLES : - - -						
						THIRD ANGLE PROJECTION						
33 8/13/13 BWG KJM RTFI UPDATED TITLE BORDER.						SS-5540/33						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER	SIZE
							CEW	12-27-84	HVP	NONE	SHT 1 OF 1	A