

Micro-Change® (M12) Jumper Cables



Female Connector


Cable

Length (m)

M12 Single I/O Multi-Port



Male Straight



Male 90°




- 1 Brown
- 2 Blue
- 3 Black
- 4 Black

WIRING CONFIGURATION

M12 Twin I/O Multi-Port



Male Straight



Male 90°




- 1 Brown
- 2 White
- 3 Blue
- 4 Black

WIRING CONFIGURATION




- 1 Brown
- 2 Black B
- 3 Blue
- 4 Black A

Micro-Change® (M12) Straight




PVC	0.6	883030E03M006	883032E03M006	884030E03M006	884032E03M006	884A30E03M006
	1.0	883030E03M010	883032E03M010	884030E03M010	884032E03M010	884A30E03M010
	2.0	883030E03M020	883032E03M020	884030E03M020	884032E03M020	884A30E03M020
	3.0	883030E03M030	883032E03M030	884030E03M030	884032E03M030	884A30E03M030
PUR	0.6	883030P03M006	883032P03M006	884030P03M006	884032P03M006	884A30P03M006
	1.0	883030P03M010	883032P03M010	884030P03M010	884032P03M010	884A30P03M010
	2.0	883030P03M020	883032P03M020	884030P03M020	884032P03M020	884A30P03M020
	3.0	883030P03M030	883032P03M030	884030P03M030	884032P03M030	884A30P03M030

Micro-Change® (M12) 90°




PVC	0.6	883031E03M006	883033E03M006	884031E03M006	884033E03M006	884A31E03M006
	1.0	883031E03M010	883033E03M010	884031E03M010	884033E03M010	884A31E03M010
	2.0	883031E03M020	883033E03M020	884031E03M020	884033E03M020	884A31E03M020
	3.0	883031E03M030	883033E03M030	884031E03M030	884033E03M030	884A31E03M030
PUR	0.6	883031P03M006	883033P03M006	884031P03M006	884033P03M006	884A31P03M006
	1.0	883031P03M010	883033P03M010	884031P03M010	884033P03M010	884A31P03M010
	2.0	883031P03M020	883033P03M020	884031P03M020	884033P03M020	884A31P03M020
	3.0	883031P03M030	883033P03M030	884031P03M030	884033P03M030	884A31P03M030

Micro-Change® (M12) PNP LED



PVC	0.6	8830P6E03M006	8830P8E03M006	8840P6E03M006	8840P8E03M006	884AP6E03M006
	1.0	8830P6E03M010	8830P8E03M010	8840P6E03M010	8840P8E03M010	884AP6E03M010
	2.0	8830P6E03M020	8830P8E03M020	8840P6E03M020	8840P8E03M020	884AP6E03M020
	3.0	8830P6E03M030	8830P8E03M030	8840P6E03M030	8840P8E03M030	884AP6E03M030
PUR	0.6	8830P6P03M006	8830P8P03M006	8840P6P03M006	8840P8P03M006	884AP6P03M006
	1.0	8830P6P03M010	8830P8P03M010	8840P6P03M010	8840P8P03M010	884AP6P03M010
	2.0	8830P6P03M020	8830P8P03M020	8840P6P03M020	8840P8P03M020	884AP6P03M020
	3.0	8830P6P03M030	8830P8P03M030	8840P6P03M030	8840P8P03M030	884AP6P03M030

Micro-Change® (M12) 90° PNP LED



PVC	0.6	8830P7E03M006	8830P9E03M006	8840P7E03M006	8840P9E03M006	884AP7E03M006
	1.0	8830P7E03M010	8830P9E03M010	8840P7E03M010	8840P9E03M010	884AP7E03M010
	2.0	8830P7E03M020	8830P9E03M020	8840P7E03M020	8840P9E03M020	884AP7E03M020
	3.0	8830P7E03M030	8830P9E03M030	8840P7E03M030	8840P9E03M030	884AP7E03M030
PUR	0.6	8830P7P03M006	8830P9P03M006	8840P7P03M006	8840P9P03M006	884AP7P03M006
	1.0	8830P7P03M010	8830P9P03M010	8840P7P03M010	8840P9P03M010	884AP7P03M010
	2.0	8830P7P03M020	8830P9P03M020	8840P7P03M020	8840P9P03M020	884AP7P03M020
	3.0	8830P7P03M030	8830P9P03M030	8840P7P03M030	8840P9P03M030	884AP7P03M030

* White not used on Single I/O and in-line splitter connectors