





RED INDICATES ORIGINAL

TABLE 1				
KEYING LETTER	A°	B°	C°	COLOR BAND
NONE	120°	120°	120°	NONE
S	135°	135°	90°	WHITE
T	100°	150°	110°	RED
U	120°	130°	110°	ORANGE
V	115°	130°	115°	YELLOW
W	125°	110°	125°	GREEN
X	130°	100°	130°	BLUE
Y	110°	140°	110°	VIOLET
Z	100°	160°	100°	GRAY

TABLE 2	
INCH	MM
.005	0.13
.015	0.38
.030	0.76
.036	0.91
.062	1.57
.125	3.18
.140	3.56
.187	4.75
.190	4.83
.380	9.65
.439	11.15
.443	11.25
.487	12.37
.500	12.70
.562	14.27
.600	15.24
.892	22.66
1.00	25.40
1.122	28.50

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS			3-0001	SH 1
REV	ECO NO.	DESCRIPTION	DWN	APPROVED
W	11328	SH-2 "D" FLAT PIN DEPTH WAS .200; B/M P/N 8-2149-3 WAS 8-2149-2; SEE ECO	SAC	Bm: FA 12/2/95



4. MAX PANEL THK .125

3. SOCKET CONTACT CONCENTRIC TWINAX/
TRIAx TRB SOLDER POT BULKHEAD
MOUNT RECEPTACLE

2. FINISH: TFS-1A(NICKEL)

1. ALL DIM ARE IN INCHES

5. EXAMPLE OF COMPLETE MODEL NO:

BASIC MODEL NO. BJ77 - T POLARIZATION LTR (SEE TABLE 1)

QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED	TROMPETER		BJ77/S/T/U/V/ W/X/Y/Z		
.XX ± .005	ELECTRONICS, INC.®				
.XXX ± .005	DWG	SAC	12-6-95	MATERIAL	CODE IDENT
.XXX ± .005	CHK	Bm	12-20-95	—	14949
SEE SH 3	ENGR	FA	12/2/95	DRAWING NO.	3-0001
NEXT ASSY	APPR	FA	12/2/95	REV	W
SCALE 4/1		DATE		11-12-68 SHEET 1C	