

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

82-28-5534

Status:

Active

Description:

1.27mm Pitch Round Conductor Flat Cable - 28 AWG (7 x 36) Stranded Topcoat, 34 Circuits, Reel 30.48m Length



Series

image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR61126
UL	E61522

General

Product Family	Cable
Series	40158
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800755000597

Physical

Cable Length	30.48m
Circuits (Loaded)	34
Insulation	PVC
Packaging Type	Reel
Pitch - Termination Interface	1.27mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	28
Wire/Cable Type	(7x36) Stranded, Topcoat

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	300V

Material Info

Old Part Number	40158-34-100B
-----------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-40158-001
---------------	--------------

EU RoHS

ELV and RoHS Compliant

REACH SVHC Not Reviewed

Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

40158Series

Use With

70121 MX-50™ Slimline Ribbon Cable.
90584 Picoflex® PF-50 IDT Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION