

FED. MFG. CODE 91929

OP-N

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.


SI	Σ
----	---

1

FO.	D
-----	---

2

DRAWN



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE --- 3 1/2 LBS MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 3/4 LB MIN		UNLESS OTHERWISE NOTED
DIFFERENTIAL TRAVEL ----- .004 MAX		DIMENSIONS ARE IN INCHES
OVERTRAVEL ----- .188 MIN		TOLERANCES ARE:
BASIC SWITCH REPLACEMENT --- BZ-2R-P4		ONE PLACE (.01) ±.030
		TWO PLACE (.001) ±.015
		THREE PLACE (.0001) ±.005
		ANGLES ±
		WEIGHT

NOTE -

- 1 - MOUNTING SCREW HOLE, 10-32UNF-2B THREAD X .219 REF DEEP (8)
- 2 - 8-32UNC X .219 REF BINDING HEAD TERMINAL SCREWS AND CUPWASHERS
- 3 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE