





TH110
PATENTED



Elevato grado di protezione
2 o 3 poli con viti imperdibili
Versione con lamella salvacavo

High protection rate
2 or 3 poles, captive screws
Wire protection version


Haut degré de protection
2 ou 3 pôles, vis imperdables
Version avec lamelle de protection

Hohes Schutzgrad
2- oder 3-polig mit Stiftschrauben
Version mit Kabelsicherungslamelle


Codice - Part number - Code - Artikel Nr.

T H B . 1 1 0 . X X X


Dati tecnici - Technical data (*)
Données techniques - Technische Daten



Versioni - Versions - Versions - Übertragung




Parti metalliche - Metal parts - Parts métalliques - Metallteile



Materia plastica - Plastic material - Matériel plastique - Plastik Stoff

Confezioni - Packaging
Emballage - Verpackung



(*) IEC 998-1 ⇒ EN 60998-1 ⇒ CEI 23.20
IEC 998-2-1 ⇒ EN 60998-2-1 ⇒ CEI 23.21

IP44

450V ~

17,5A

1,5

Ottone nichelato
Nickled brass
Laiton nichelé
Vernickeltem Messing



Acciaio zincato passivato
Zinc passivated steel
Acier zinqué passivé
Zinkpassivierte Stahl



PA66 UL94 V0 GWT 960°C
Nero - Black
Noir - Schwartz

T125

155°C

PA66 UL94 V2 GWT 850°C
Naturale - Natural
Naturel - Ungefärbt

T85

115°C