

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19200-0014

Status:

Active

Overview:

Splices

Description:

Avikrimp™ Seamless Butt Splice for 18-22 AWG Wire, Super Duty

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Splices
Series	19200
Comments	Red
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Avikrimp™
UPC	756054494233

Physical	
Barrel Type	Closed
Color - Resin	Red
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	154.400/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	3.50mm
Wire Size AWG	18, 20, 22

Electrical	
Voltage - Maximum	600V

Material Info	
Old Part Number	AS-845 BAG100

Reference - Drawing Numbers	
Product Specification	PS-19902-011
Sales Drawing	SD-19200-001



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19200Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19200-0014](#)