



C-101



Technical drawing of a double sink unit with the following dimensions and features:

- Overall width: 46 mm
- Overall height: 46 mm
- Overall depth: 29 mm
- Left sink width: 10 mm
- Left sink depth: 26 mm
- Right sink width: 10 mm
- Right sink depth: 28 mm
- Overall length: 47 mm
- Overall width (45.5 mm): 26 mm + 10 mm + 10 mm
- Left side thickness: 13 mm
- Right side thickness: 5 mm
- Front thickness: 13.5 mm
- Front edge radius:  $\phi 4$
- Left side countersink: 2-φ 3.3 mm,  $\phi 6.5$  mm
- Right side countersink: 3-φ 3.3 mm,  $\phi 6.5$  mm

※本図は締代0mmの場合です。

※Drawings show the tightening margin of 0mm

商品番号 Product No.	RoHS 10/4 	コード Code	単価 Price	量販価格 Bulk Price	
				数量 Quantity	単価 Price
C-1013	 2D/3D	21460	¥690	20個～	¥662

● RoHS10指令対応品

●: ROHS10指令対応品  
▲: RoHS10指令に対応可能です

※大量のご注文は重にお安くなります

PAT.PEND

- 鍵は360°回転で施錠時、解錠時ともに抜差しできます。
  - ステンレス製で耐食性に優れています。
  - Key can be inserted/removed at 360° turn both when locking and unlocking.
  - Corrosion-resistant stainless steel is used.

仕様 ● 製品質量: 60g

- ・材質: 冷間圧延ステンレス鋼板(SUS304)
  - ・表面仕上: バレル研磨
  - ・付属品: キー2本

## 用 途 • 計測機器・船用機器・医療機器

納期 ● 標準在庫品

Specifi- • Mass: 60g

- Material: Cold rolled stainless steel plate (SUS304)

- Finish: Barrel surface polishing

- Accessories: Two keys

Specific use • Measuring, ship and medical equipment

使用例

## Example of application

